


NARS2 Antibody (C-term)

Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP7585b	WB, IHC, E	H	Q96I59
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB15140

Application Data:

Calculated MW: 54077 Da



Western blot analysis of anti-NARS2 Antibody (C-term) (Cat.#AP7585b) in HeLa cell line lysates (35ug/lane). NARS2 (arrow) was detected using the purified Pab (1:60 dilution).



Formalin-fixed and paraffin-embedded human prostate carcinoma tissue reacted with NARS2 antibody (C-term) (Cat.#AP7585b), which was peroxidase-conjugated to the secondary antibody, followed by DAB staining. This data demonstrates the use of this antibody for immunohistochemistry; clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
79731	NARS2

Other Names:

Probable asparaginyl-tRNA synthetase, mitochondrial [Precursor]; EC 6.1.1.22; Asparagine--tRNA ligase; AsnRS; NARS2

Target/Specificity:

This NARS2 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 448~477 amino acids from the C-terminal region of human NARS2.

Application Notes:

The suggested dilution is:

ELISA 1:1,000
Western blotting 1:50~100
Immunohistochemistry 1:10~50

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is prepared by Saturated Ammonium Sulfate (SAS) precipitation followed by dialysis against PBS.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

NARS2 Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.
