


HARS Antibody (N-term)

Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP7567a	WB, IHC, E	H	P12081

Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB14816

Application Data: **Calculated MW: 57411 Da**



Western blot analysis of anti-HARS Pab (Cat.#AP7567a) in K562 cell line lysates (35ug/lane). HARS (arrow) was detected using the purified Pab (1:60 dilution).



Formalin-fixed and paraffin-embedded human hepatocarcinoma tissue reacted with HARS antibody (N-term) (Cat.#AP7567a), which was peroxidase-conjugated to the secondary antibody, followed by DAB staining. This data demonstrates the use of this antibody for immunohistochemistry; clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
3035	HARS

Other Names:

Histidyl-tRNA synthetase, cytoplasmic; Histidine--tRNA ligase; HisRS; HARS; HRS

Target/Specificity:

This HARS antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 56~86 amino acids from the N-terminal region of human HARS.

Application Notes:

The suggested dilution is:
 ELISA 1:1,000

Western blotting 1:50~100
Immunohistochemistry 1:10~50

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is prepared by Saturated Ammonium Sulfate (SAS) precipitation followed by dialysis against PBS.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

HARS Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
