


PUM2 Antibody (N-term)

Peptide Affinity Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP7569b	WB, IHC, E	H	Q8TB72
Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB10534

Application Data:

Calculated MW: 114216 Da



Western blot analysis of PUM2 (arrow) using rabbit polyclonal PUM2 Antibody (N-term) (Cat.#AP7569b). 293 cell lysates (2 ug/lane) either nontransfected (Lane 1) or transiently transfected with the PUM2 gene (Lane 2) (Origene Technologies).



Formalin-fixed and paraffin-embedded human testis tissue reacted with PUM2 Antibody (C-term) (Cat.#AP7569b), which was peroxidase-conjugated to the secondary antibody, followed by DAB staining. This data demonstrates the use of this antibody for immunohistochemistry; clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
23369	PUM2

Other Names:

Pumilio homolog 2; Pumilio-2; KIAA0235; PUMH2; PUM2; Pumilo 2

Target/Specificity:

This PUM2 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 140~170 amino acids from the N-terminal region of human PUM2.

Application Notes:

The suggested dilution is:
ELISA 1:1,000

Western blotting 1:50~100
Immunohistochemistry 1:10~50

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is purified through a protein A column, followed by peptide affinity purification.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

PUM2 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.
