


## ACPP Antibody (C-term)

### Purified Rabbit Polyclonal Antibody (Pab)


Catalog #	Applications:	Reactivity:	Accessions:
AP7592b	WB, IHC, E	H	<a href="#">P15309</a>

Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB15146

#### Application Data: Calculated MW: 44566 Da



Western blot analysis of anti-ACPP Antibody (C-term) (Cat.#AP7592b) in mouse lung tissue lysates (35ug/lane). ACPP (arrow) was detected using the purified Pab (1:60 dilution).



Formalin-fixed and paraffin-embedded human lung carcinoma tissue reacted with ACPP antibody (C-term) (Cat.#AP7592b), which was peroxidase-conjugated to the secondary antibody, followed by DAB staining. This data demonstrates the use of this antibody for immunohistochemistry; clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
<a href="#">55</a>	ACPP

#### Other Names:

Prostatic acid phosphatase [Precursor]; PPAP; EC 3.1.3.2; ACPP

#### Target/Specificity:

This ACPP antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 320~349 amino acids from the C-terminal region of human ACPP.

#### Application Notes:

The suggested dilution is:  
ELISA 1:1,000

Western blotting 1:50~100  
Immunohistochemistry 1:10~50

---

**Format:**

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is prepared by Saturated Ammonium Sulfate (SAS) precipitation followed by dialysis against PBS.

---

**Storage:**

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

---

**Precautions:**

ACPP Antibody (C-term) is for research use only and not for use in diagnostic or therapeutic procedures.

---