PHACTR2 Antibody (N-term)


Purified Rabbit Polyclonal Antibody (Pab)

Catalog #	Applications:	Reactivity:	Accessions:
AP7618a	WB, IHC, E	H	O75167


Concentration:	Size:	Isotype:	Clone Name:
0.25 mg/ml	0.1 mg	Rabbit Ig	RB18550

Application Data:

Calculated MW: 69700 Da



Western blot analysis of PHACTR2 antibody (N-term) (Cat. #AP7618a) in HepG2, 293, K562 and Hela cell line lysates (35ug/lane). PHACTR2 (arrow) was detected using the purified Pab.



Formalin-fixed and paraffin-embedded human hepatocarcinoma reacted with PHACTR2 Antibody (N-term), which was peroxidase-conjugated to the secondary antibody, followed by DAB staining. This data demonstrates the use of this antibody for immunohistochemistry; clinical relevance has not been evaluated.

Gene ID:	Gene Symbol:
9749	PHACTR2

Other Names:

Phosphatase and actin regulator 2 ; KIAA0680; C6orf56; PHACTR2

Target/Specificity:

This PHACTR2 antibody is generated from rabbits immunized with a KLH conjugated synthetic peptide between 176~206 amino acids from the N-terminal region of human PHACTR2.

Application Notes:

The suggested dilution is:
ELISA 1:1,000

Western blotting 1:50~100
Immunohistochemistry 1:50~100

Format:

Purified polyclonal antibody supplied in PBS with 0.09% (W/V) sodium azide. This antibody is prepared by Saturated Ammonium Sulfate (SAS) precipitation followed by dialysis against PBS.

Storage:

Maintain refrigerated at 2-8°C for up to 6 months. For long term storage store at -20°C in small aliquots to prevent freeze-thaw cycles.

Precautions:

PHACTR2 Antibody (N-term) is for research use only and not for use in diagnostic or therapeutic procedures.